

Collision Repair Aligner Ordering Guide

Step 1 Choose your Aligner Console and Sensors – (WA600 and Hawkeye Elite CM recommended)

Console: _____

Sensors: _____



Step 2 Add Essential Collision Alignment Accessories



- ☐ **20-2511-1**
Wide Angle Target Extensions
for Advanced Diagnostic
Angle measurement such as
Max Steer



- ☐ **20-2664-1**
Wheel Off Adaptors



- ☐ **20-2882-1**
Cordless Remote Indicator

☐ Other customer requested
accessories:

Step 3 Add Portable Turnplate Kit, Wheel Stands, or Alignment Rack



- ☐ **20-2679-1**
Portable Turnplate kit
(fits Chief®, Car-o-
Liner®, and most other
leading brands)



- ☐ **JB-A**
JB Wheel Stands (for use
with frame contact lifts)

Also required:

- ☐ **25-171-1** Red 14" turnplate kit (2 required)
Also available in stainless steel.
- ☐ **51-754-1** Rear slipplate (2 required)




- ☐ Add an alignment rack

Model: _____

HUNTER
Engineering Company
www.hunter.com

Collision Repair Aligner Ordering Guide



Car-o-Liner® example



Chief® example

HUNTER
Engineering Company
www.hunter.com